

P.S. FILM EXTRA

Description PU plotter cut heat seal material with polyester backing. Very thin and suggested for “difficult” fabrics such as windbreakers, K-Way, nylon, leather, sports bags, umbrellas. The material is certified Öko-Tex® Standard 100 Class I

Average film thickness before transfer: **90 micron**

Usage informations Due to the many different base materials available on the market, the following instructions are given as a guideline only :

Plotter settings (eg. with SUMMACUT D60 – ROLAND GX24)

Blade: **new at 50°**

Minimum cutting pressure: **50 gf**

Transfer setup

Temperature: **160 °C (320°F)**

Time: **15 seconds**

Pressure: **medium (3÷4 bar)**

Procedure **N.B.: if applied onto treated fabrics, we recommend to perform a prior application and washing test.**

Mirror cut the material

Weed the exceeding material (for a quick and easier weeding, we suggest to place the cut material for a few seconds on a warm surface such as the plates, 60-70°C)

Place the material on the garment with its polyester backing

Heat apply

Remove the support warm or cold

Certifications



The product is REACH approved
The product is certified Öko-Tex® Standard 100 Class I

Suitable textiles Polyamide, nylon and treated materials (not suited for dye sublimation fabrics)

Washing instructions Wait **24h** after the heat transfer
40°C
Do not use bleach or other aggressive chemical agents.
Dry clean: **no**
Tumble dry: **yes**



Siser s.r.l.

N.B. All information given in this sheet are based on our experience.
We always recommend performing a test before starting standard production.
For best results we recommend to store the product away from direct sunlight.

Viale della Tecnica n° 18
36100 Vicenza - Italy
Tel. +39 0444.287960
Fax +39 0444.287959
info@siser.it - www.siser.it

The product meets the Italian and EU regulations relating to its proper use, and to the (EU) regulation n. 1907/2006/EU REACH (Registration, Evaluation, Authorization and Restriction of Chemical substance). This document can be subject to variations. Updated versions are available on our website www.siser.it. For further information, please contact our Sales Office.
Thank you.